



## Mosaic™ Cable outlets and branching device


Cat. No(s): 0 775 50/51/52/53 - 0 791 50 - 0 792 49



0 775 52



0 775 51



0 775 53


### 1. USE

Cable outlets and wires for cables of different diameters.  
 Mechanisms are flush-mounted or surface-mounted.

### 2. RANGE

	White	Anthracite	Aluminium
Branching device with 3 terminals 2 modules	0 775 53	-	-
Equipped cable outlet with cable clamps max. Ø to be used 12 mm, min. Ø to be used 4 mm 2 modules	0 775 51	-	-
Cable outlet with cable clamps max. Ø to be used 12 mm, min. Ø to be used 4 mm Authorized cables H05 VVF or H07 RNF 2 modules	0 775 50	0 791 50	0 792 49
Wire outlet Ø 8 mm 1 module	0 775 52	-	-

### 3. DIMENSIONS (mm)



Cat. Nos	A	B	C	D
0 775 50 - 0 791 50 - 0 792 49	45	45	39	20
0 775 51	45	45	49.5	20
0 775 52	45	22.5	24.5	-
0 775 53	45	45	32.5	12.5

### 4. CONNECTION

#### Cat. No 0 775 51

Type of terminals: automatic  
 Stripping length: 12 mm  
 Cable cross-section: 4 x 2 x 1.5 mm<sup>2</sup>

#### Cat. No 0 775 53

Type of terminals: with screws  
 Stripping length: 12 mm  
 Cable cross-section: 6 x 2.5 mm<sup>2</sup>  
 Screwdriver: Philips n° 1

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 41  
 Protection against impact: IK 04

#### ■ 5.2 Material characteristics

Base: PC  
 Cover plate: PC White (RAL 9003)  
 ABS Anthracite for Cat. No 0 791 50

Halogen free  
 UV resistant  
 Self-extinguishing: 650° C / 30 s

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
 Current: 10 A for Cat No 0 775 51  
 20 A for Cat No 0 775 53

#### ■ 5.4 Climatic characteristics

Storage temperature: - 10° C to + 70° C  
 Use temperature: - 5° C to + 35° C

### 6. CLEANING

Surface cleaning with a cloth.  
 Do not use: acetone, tar remover, trichloroethylene.  
 Resistance to the cleaning agents: Hexane (NF C 61-314), Methylated spirit, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning substances, Pre-impregnated wipes.  
 Anios, Surfianios, Bactylisine, Diluted hydrogen peroxide (35 %).

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
 See e.catalogue.