



**Forix™ - IP 44**  
**German sockets**


Cat. No(s): 7 823 71/72/73/74/91/92/93/94



7 823 73/93



7 823 74/94



7 823 72/92


**1. USE**

General 16 A german socket outlet.  
 Mechanisms with single, large rocker can be illuminated using lamp  
 Cat. No. 7 823 98.

**2. RANGE**

| Finishes |          | Designation                       |
|----------|----------|-----------------------------------|
| White    | Grey     |                                   |
| 7 823 73 | 7 823 93 | 2 P+E socket                      |
| 7 823 74 | 7 823 94 | 2 x 2 P+E socket                  |
| 7 823 71 | 7 823 91 | One-way switch + 2 P+E socket     |
| 7 823 72 | 7 823 92 | Double pole switch + 2 P+E socket |

**3. OVERALL DIMENSIONS**



| Cat. No.    | A   | B  | C  |
|-------------|-----|----|----|
| 7 823 73/93 | 70  | 70 | 57 |
| 7 823 71/91 | 140 | 70 | 57 |
| 7 823 72/92 | 140 | 70 | 57 |
| 7 823 74/94 | 140 | 70 | 57 |

**4. CONNECTION**

Stripping: 10 mm  
 Terminal type: with screws  
 Terminal capacity up to: 2 x 2.5 mm<sup>2</sup>  
 Recommended screwdriver size: pozidrive No 2  
 Recommended tightening torque: 0.5 Nm for switch  
 0.8 Nm for socket

**5. TECHNICAL CHARACTERISTICS**

■ **5.1 Mechanical characteristics**

Protection against liquids: IP 44  
 Impact tests: IK 07

■ **5.2 Material characteristics**

Box: ABS  
 Rocker: ABS  
 Mechanism: PC  
 Conduit gland: SEBS

■ **5.3 Electrical characteristics**

Voltage: 250 VAC  
 Current: 10 AX for switch  
 16 A for socket

■ **5.4 Climatic characteristics**

Storage and use temperature: - 25° C to + 60° C

**6. CLEANING**

Surface cleaning with a cloth.  
 Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane (EN 60669-1), Methylated spirits, Soapy water, Diluted ammonia, Diluted pure bleached 10%, Glass cleaning substance, Pre-impregnated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

**7. ACCESSORIES**

■ **7.1 Lamps**

Become illuminated with lamp Cat. No 7 823 98

■ **7.2 Spare membrane glands**

White membrane Cat. No 7 823 79  
 Grey membrane Cat. No 7 823 99